


General Features



Properties of the TOCON_blue2

- GaP detector for blue light radiation
- detection of incoherent blue light acc. to guideline 2006/25/EG
- 170 $\mu\text{W}/\text{cm}^2$ peak radiation results a voltage of approx. 2 V
- RoHS compliant
- Applications: measurement of low blue light irradiation, occupational safety


The TOCON pre-amplified photodetectors

The TOCON devices are using modern hybride technology to cancel unwanted signal disturbances caused by moisture or electromagnetic radiation. The stable 0...5V output voltage can be directly connected to a SPC controller or a voltage multimeter. No external amplifier is needed.


Specifications

Parameter	Symbol	Value	Unit
Maximum Ratings			
Operating Temperature Range	T_{opt}	-25 ... +85	$^{\circ}\text{C}$
Storage Temperature Range	T_{stor}	-40 ... +100	$^{\circ}\text{C}$
Soldering Temperature (5s)	T_{sold}	300	$^{\circ}\text{C}$
General Characteristics ($T=25^{\circ}\text{C}$, $V_{\text{supply}}=+5\text{ V}$)			
Supply voltage	V_{supply}	2,5 ... 5,0	V
Saturation voltage	V_{sat}	V_{supply}	V
Dark offset voltage	V_{offset}	0,05	mV
Temperature coefficient of V_{offset}	T_{co}	<7	%/K
Current consumption	I	0,8	mA
Spectral Characteristics ($T=25^{\circ}\text{C}$, $V_{\text{supply}}=+5\text{ V}$)			
Sensitivity at peak	S_{max}	12	$\text{mV}/\mu\text{W}/\text{cm}^2$
Wavelength of max. spectral sens.	λ_{max}	445	nm
Sensitivity range ($S=0,1*S_{\text{max}}$)	-	390 ... 515	nm


Spectral Response



Drawing



Field of View



TOCON Product Portfolio

Selection of TOCONs for blue light radiation:

Option	Approx. min irradiance	Approx. max irradiance ($V_{supply} = 5V$)
TOCON_blue1	4,2 nW/cm ²	43 μ W/cm ²
TOCON_blue2	42 nW/cm²	430 μW/cm² this device
TOCON_blue3	420 nW/cm ²	4,3 mW/cm ²
TOCON_blue4	4,2 μ W/cm ²	43 mW/cm ²
TOCON_blue5	42 μ W/cm ²	430 mW/cm ²
TOCON_blue6	420 μ W/cm ²	4,3 W/cm ²

TOCONs are also available with other spectral sensitivity (UV broadband, UVA, UVB, UV-Index, UVC).

Upgrades

TOCON housings for easy mounting of the TOCON_blue2

TOCON_housing



Advantages of the TOCON_housing

- Easy to mount and connect
- Robust stainless steel M12x1 thread body, length 32 mm
- Integrated sensor connector (Binder 5-Pin plug)
- Comes with 2 m connector cable

TOCON_PTFE_housing



Advantages of the TOCON_PTFE_housing

- Easy to mount and connect, cleanable
- Dirt-repellant, water proof at wetside (IP 68)
- Teflon (PTFE) M12x1 thread body, length 31 mm
- Wide field of view
- Integrated sensor connector (Binder 5-Pin plug)
- Comes with 2 m connector cable

The PTFE housing reduces the signal output by 95 %.

Sensor Monitor 5.0 for monitoring, datalogging and process control with TOCON_blue2



The **Sensor Monitor 5.0** series are measurement and control modules for monitoring and automation of irradiation processes. They display radiation, dose and state information.

A selection of devices with one or two channels, optional USB & RS232 data output and computer software is offered.

UVMICROLOG for datalogging and permanent measurements with TOCON_blue2



The **UVMICROLOG** is designed for logging of blue light radiation, temperature, pressure and acceleration. Sophisticated microcontroller technology allows up to 3 months of permanent measurement and logging without battery charging. The unit can be mounted with a belt or screws.